

Electro Coagulation Setup



Electro Coagulation Setup

| | |
|--------------------------------|---|
| Feed Tank | PE – 70 lit – heater – mixer – PH control |
| Flocculation Tank | SS – 18 lit – heater – mixer – PH control |
| Product Tank | PE – 70 lit |
| Additive Tank | Glass – 2 lit – 6 set |
| Additive dosing pump | 0 - 250 ml/min – 6 set |
| Feed pump | Peristaltic pump , 0 -1500 ml/min |
| Recycling pump | |
| DC Rectifier | 0 - 30 V , 0 - 20 A |
| EC Rector | SS – Heater – Cooler – 0.5 lit Air Injection System – PH control |
| EF Reactor | SS – Heater – Cooler – 1.5 lit Air Injection System – PH control |
| CC Reactor | SS – Heater – Cooler – 1.5 lit – mixer Air Injection System – PH control |
| Air Compressor | 0 - 1 ft3/min , 0 - 2 bar |
| Power and Control Cabin | Touch screen HMI + PLC control |